


# HP-PESE Series

## Polyethersulfone – Electronic Grade



## Applications

- DI Water
- Microelectronics
- Process Water
- RO Pre/Postfiltration
- Semiconductors
- Water and Wastewater



## Commercial/Industrial Filtration Applications

### Standard Features

- Manufactured in the USA
- Absolute retention ratings from 0.03 to 0.65 microns
- 7.2 sq. ft. (0.67 m<sup>2</sup>) of media surface area per 10" length for optimal performance
- 100% flushed w/18 megohm DI water to less than 5 ppb TOC
- Rapid rinse-up to 18 megohm resistivity and low extractables for use in ultrapure water
- Manufactured in a Class 10,000 Clean Room environment for high purity
- Rigid, molded cage protects pleated media and strengthens structural stability
- Available up to 40 inches in length (10 inch modules)

## Product Specifications

### Micron Sizes

0.03, 0.1, 0.2, 0.45, and 0.65

### Cartridge Lengths

9-3/4" (24.7 cm), 10" (25.4 cm), 20" (50.8 cm), 30" (76.2 cm), and 40" (101.6 cm)

### Inside and Outside Diameters

1" (2.54 cm) ID, 2.67" (6.78 cm) OD

### Media Surface Area

7.2 sq. ft. (0.65 m<sup>2</sup>) per 10" filter length

### Maximum Operating Temperature

176 °F (80 °C) temperature limit

### Recommended Change-Out Differential Pressure

35 psid (2.4 bar)

### Maximum Differential (Collapse) Pressure

75 psid@70 °F (5.2 bar@21 °C), 40 psid@176 °F (2.8 bar @80 °C)

### Sanitization and Sterilization

Hot water at 175 °F (80 °C) at 5 psid for 30 minutes

Inline steam at 257 °F (125 °C) @ 1 psid (0.7 bar) for 30 minutes

Autoclavable at 257 °F (125 °C) for 30 minutes

### Materials of Construction

Filter media: asymmetric polyethersulfone

Outer cage, inner core and end caps: polypropylene

### FDA and USP Compliance


All filters manufactured of virgin polypropylene materials. All polypropylene materials comply with the requirements of Food and Drug Administration Title 21 of The Code of Federal Regulations 174.5, 177.1520 and 177.1630. All components meet current USP Class VI biological tests for plastics.

# Ordering Guide (Example: HP-PESE-26100-0.2213-B-HT)

HP	-	PESE	-	26	100	-	0.2	213	-	B	-	HT
TYPE		MEDIA		CARTRIDGE DIAMETER	CARTRIDGE LENGTH		MICRON RATING		END CAP		O-RING / GASKETS	OPTIONS
HP = High Purity Pleating		PESE = Polyethersulfone (electronic grade)		26 = 2.67" (6.78 cm)	097 = 9-3/4" 100 = 10" 200 = 20" 300 = 30" 400 = 40"		0.03 = 0.03 0.1 = 0.1 0.2 = 0.2 0.45 = 0.45 0.65 = 0.65		Blank = DOE (standard) 213 = 213 internal o-ring 222f = 222/Flat 222n = 222/Fin 222s = 222/Spring 226f = 226/Flat 226n = 226/Fin SOEf = SOE/Flat SOEn = SOE/Fin SOEs = SOE/Spring Z = Custom		E = EPDM B = Buna N S = Silicone V = Viton T = Teflon	HT = High Temp (200 °F, 93 °C)*

\*High temperature construction (cage, core, end caps): maximum temperature 200 °F (83.3 °C) – available only in 222 or 226 with fin or flat end caps.

## Flow vs. Pressure Drop



This chart represents the typical water flow per 10" cartridge length. Cartridges are tested in water at ambient temperature. Data may be extrapolated for multiple lengths, but as flow rate increases, ΔP of the housing becomes more apparent.

## Integrity Testing

PORE SIZE	AIR DIFFUSION RATE
0.03µm	≤30cc/min@60psi
0.1 µm	≤30cc/min@48psi
0.2 µm	≤30cc/min@35psi
0.45µm	≤30cc/min@20psi
0.65µm	≤30cc/min@15psi
Per 10" length water wetted membrane	


## Case Packs

Each high purity cartridge is individually poly bagged and individually boxed, then master packed into cartons of 12 units in all lengths.



**Filter Housings Selection Guide**  
CLICK HERE

## Available End Cap Configurations



All illustrations © Copyright 2014 NeoLogic Solutions. All Rights Reserved.



Contact your **authorized NeoLogic distributor** today:  
**Commercial Industrial Supply**  
 1444 E. Main St., Rock Hill, SC 29730  
 Tel: (866) 777-8001 Email: info@emailcis.com